

With the VITO® Oil Filter System, you can almost double the life of your frying oil and improve the quality of your fried product while saving time and money. A unique solution providing the combined benefits of reduced costs, better quality frying, less frequent oil changes and higher quality product to your customers. Simply place VITO® in the fryer unit and filtration is completed automatically. No need to drain your fryers and no need to pay for outsourcing expensive filtration services. Choose the unit that suits your operation and start saving up to 50% on your frying oil costs. The optional VITO® FOM330 Oil Tester can monitor oil quality and provide data that ensures consistent quality and proper oil replacement schedules to save even more.

**FSM** 

(FOOD SERVICE MACHINERY PTY. LTD.)

21-23 Agosta Drive, Laverton North, Vic. 3026 Australia

T: +61 3 9368 2300 F: +61 3 9369 3800 E: sales@fsm-pl.com.au W: www.fsm-pl.com.au SYDNEY OFFICE

Unit 15, 7-9 Progress Circuit,
Prestons, NSW 2170
T: +61 2 9608 8620 F: +61 2 9607 9370
E: sales@fsm-pl.com.au W: www.fsm-pl.com.au

QUEENSLAND OFFICE:

4/40 Rivergate Place, Murarrie, QLD 4172 T: +61 7 3390 4185 F: +61 7 3393 9508 E: sales@fsm-pl.com.au W: www.fsm-pl.com.au PERTH:

T: 0413 893 311 E: sales@fsm-pl.com.au W: www.fsm-pl.com.au

### Choose the correct model for your fryer capacity



VITO®30 up to 12 Litres



VITO<sup>®</sup>50 up to 20 Litres



VITO<sup>®</sup>80 over 20 Litres



VITO FOM330 OIL TESTER

# VITO portable

#### The world's best in-tank pressure oil filtration system!







made in Germany



**VITO 30** 



VITO 50
1-4 fryers up to 201
For light to medium



VITO 80
All fryers or heavy duty.
For medium to heavy
sediment.

	Filtration power	Filtration efficiency	Particle uptake	Work cycle	Suction depth	Weight	Temperature	Material VITO	Particle filter
VITO 30	up to 30I /min	up to 5ųm	0,8kg	4,5min	~ 20cm	6,3kg	max. 200°C	Stainless steel 1.4301	Cellulose FDA-CFR 21
VITO 50	up to 50l/min	up to 5ųm	1,3kg	4,5min	~ 35cm	7,7kg	max. 200°C	Stainless steel 1.4301	Cellulose FDA-CFR 21
VITO 80	up to 80I/min	up to 5ųm	2,5kg	4,5min	~ 45cm	9,2kg	max. 200°C	Stainless steel 1.4301	Cellulose FDA-CFR 21

Due to our policy of continual improvement, descriptions and technical information may change without notice.

21-23 Agosta Drive, Laverton North,
Vic. 3026 Australia
T: +61 3 9368 2300 F: +61 3 9369 3800
E: sales@fsm-pl.com.au W: www.fsm-pl.com.au

#### SYDNEY OFFICE

Unit 15, 7-9 Progress Circuit, Prestons, NSW 2170 T: +61 2 9608 8620 F: +61 2 9607 9370 E: sales@fsm-pl.com.au W: www.fsm-pl.com.au

## **QUEENSLAND OFFICE:** 4/40 Rivergate Place,

### Arvergate Place,

Murarrie, QLD 4172
T: +61 7 3390 4185 F: +61 7 3393 9508
E: sales@fsm-pl.com.au W: www.fsm-pl.com.au

#### PERTH:

T: 0413 893 311 E: sales@fsm-pl.com.au W: www.fsm-pl.com.au